




Utan S-krok

77



Med S-krok


137



Art.nr.	X	Name	X						
Last saved by	Jonathan	Last saved	2018-08-29	Material	X	Rev	-	Format	A4
Created by	Jonathan	Created date	2018-05-21	Scale	1:6	Page	1/1		



Utan S-krok

101





Med S-krok

160





**GÖTESSONS**

Art.nr.	X	Name	X						
Last saved by	Jonathan	Last saved	2019-09-12	Material	X	Rev	-	Format	A4
Created by	Jonathan	Created date	2018-05-21	Scale	1:6	Page	1/1		



Art.nr.		Name		
X		X		
Last saved by	Last saved	Material	Rev	Format
Jonathan	2018-08-29		-	A4
Created by	Created date	X	Scale	Page
Jonathan	2018-05-21		1:8	1/1



**Distans mellan absorbenter =  
total längd på hängkrok + 54mm**



Art.nr.		Name		
X		X		
Last saved by	Last saved	Material	Rev	Format
Jonathan	2018-08-29		-	A4
Created by	Created date	X	Scale	Page
Jonathan	2018-05-21		1:10	1/1